


HEAT SHRINK TUBING



✓ Active

> [See All Documentation](#)

TE CONNECTIVITY
HRHT-2/6
 Raychem | HRHT

HRHT-2/6
 TE Internal Number: 693432-000
 Alias ID: 7-1198822-6

Not reviewed for RoHS Compliance

Wall Type **Single**

Resistant To **Abrasion**

Low Outgassing **No**

Product Source **US**

Packaging Method **Piece**

> [See All Features](#)

North America ▼

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION >

- [GET SAMPLE](#)
- [SAVE TO LIST](#)
- [CHECK FOR TOOLING](#)
- [FIND SIMILAR PRODUCTS](#)

DOCUMENTATION FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features	Wall Type	Single
	Product Family	HRHT
Body Features	Shrink Ratio	6:1
	Color	Black
	Material	Irradiated Modified Polyolefin
	Fluid Type	Water
Dimensions	Recovered Inside Diameter (Max)(mm)	5.84
	Recovered Wall Thickness (Tolerance)(mm)	3.94
	Expanded Inside Diameter (Min)(in)	1.5
	Cut Length	152.4mm[6in]
Usage Conditions	Resistant To	Abrasion
	Recovery Temperature(°C)	150
	Flammability	Flame-Retardant
	Fluid Resistance	Splash Protection
	Shrink Temperature (Min)(°C)	135
Product Availability	Applicable Region	Global
Packaging Features	Packaging Method	Piece
Other	Low Outgassing	No
	Product Source	US
Product Compliance	Statement of Compliance PDF VIEW ALL PRODUCT COMPLIANCE	

COMPATIBLE

No compatible products found for HRHT-2/6