

EG 45-GP/ABS GN - Mounting base housing



2764153

<https://www.phoenixcontact.com/us/products/2764153>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Component housing, Lower housing part, with snap-on foot and test opening with side cover, without vents, width: 45 mm, height: 75 mm, color: green (similar RAL 6021), cross connection: without bus connector, number of positions cross connector: not relevant

Your advantages

- Tool-free mounting

Commercial data

Item number	2764153
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	AC11
Product key	ACHCGA
GTIN	4017918065867
Weight per piece (including packing)	52.74 g
Weight per piece (excluding packing)	53.6 g
Customs tariff number	85389099
Country of origin	PL

EG 45-GP/ABS GN - Mounting base housing



2764153

<https://www.phoenixcontact.com/us/products/2764153>

Technical data

Product properties

Product type	Enclosure bottom part
Housing type	Component housing
Housing series	EG
Product family	EG...G
Type	Lower housing parts with test opening with side cover, housing cover necessary to complete the module
Number of positions	16
Max. number of positions	0)
Type	Lower housing part, with snap-on foot and test opening with side cover
Ventilation openings present	no

Dimensions

Dimensional drawing	
Width	45 mm
Height	75 mm

PCB design

PCB thickness	1.4 mm ... 1.8 mm
---------------	-------------------

Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	HB
Housing material	ABS
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Max. IP code to attain	IP20
Ambient temperature (operation)	-40 °C ... 80 °C (depending on power dissipation)
Ambient temperature (storage/transport)	-40 °C ... 55 °C
Ambient temperature (assembly)	-5 °C ... 80 °C

PCB data

EG 45-GP/ABS GN - Mounting base housing



2764153

<https://www.phoenixcontact.com/us/products/2764153>

Thickness of the PCB	1.4 mm ... 1.8 mm
----------------------	-------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------


EG 45-GP/ABS GN - Mounting base housing

2764153

<https://www.phoenixcontact.com/us/products/2764153>



Drawings




EG 45-GP/ABS GN - Mounting base housing

2764153

<https://www.phoenixcontact.com/us/products/2764153>



Dimensional drawing




Component mounting side, if the double-level upper part is used


EG 45-GP/ABS GN - Mounting base housing

2764153

<https://www.phoenixcontact.com/us/products/2764153>



valid for PCB 1; 3; 5 and 6, see explosion drawing




valid for PCB 7 and 12, see explosion drawing

EG 45-GP/ABS GN - Mounting base housing

2764153

<https://www.phoenixcontact.com/us/products/2764153>




valid for PCB 10, see explosion drawing

EG 45-GP/ABS GN - Mounting base housing

2764153

<https://www.phoenixcontact.com/us/products/2764153>




valid for PCB 13

EG 45-GP/ABS GN - Mounting base housing

2764153

<https://www.phoenixcontact.com/us/products/2764153>



valid for PCB 14

EG 45-GP/ABS GN - Mounting base housing



2764153

<https://www.phoenixcontact.com/us/products/2764153>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2764153>



UL Recognized

Approval ID: E240868

EG 45-GP/ABS GN - Mounting base housing



2764153

<https://www.phoenixcontact.com/us/products/2764153>

Classifications

ECLASS

ECLASS-13.0	27190601
ECLASS-15.0	27190601

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

EG 45-GP/ABS GN - Mounting base housing



2764153
<https://www.phoenixcontact.com/us/products/2764153>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com