Part Number : 191310044
Product Description : InsulKrimp Block Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 4 (M2.6), Length 18.47mm
Series Number : 19131
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : AA-2109-04XT



Documents and Resources

Drawings

191310044_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-009-001.pdf

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

Downloaded from Arrow.com.

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19131
Description	InsulKrimp Block Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 4 (M2.6), Length 18.47mm
Keyword	Spade Terminal, Spade Terminals
Product Name	InsulKrimp
Style	Spade Block
Type	Spade Connector
UPC	800753101661

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Color - Resin	Natural
Flammability	94V-0

Downloaded from Arrow.com.

Insulation	PVC
Material - Plating Mating	Tin
Net Weight	0.517/g
Packaging Type	Adhesive Tape on Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	3-4 (M2.6)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	3.70mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.35-0.80

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	192310584
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880023
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	638851300

Downloaded from Arrow.com.