


D-SUB STANDARD

Solder pin – Angled – .370" / 9.4 mm – Stamped contacts




RoHS compliant – CSA listed, File No.: LR 115000-1 – UL listed, File No.: E202784


SOCKET CONNECTOR



Mounting style: PCB clip, front spacer




No. of pos.	A -0.76	B -0.25	C
09	31.19	16.46	25.00 +0.12
15	39.52	24.79	33.30 +0.15 -0.10
25	53.42	38.50	47.04 +0.13
37	69.70	54.96	63.50 +0.13




DESCRIPTION

- Mounting style:
with mounting bracket, PCB clip and 4-40 UNC hex bolt
- Quality class 3 (other quality classes on request)
- Shell: Steel tin plated


PLUG CONNECTOR



Mounting style: PCB clip, front spacer



No. of pos.	A -0.76	B +0.25	C	D -0.3
09	31.19	16.79	25.00 +0.12	6.12
15	39.52	25.12	33.30 +0.15 -0.10	6.12
25	53.42	38.84	47.04 +0.13	5.99
37	69.70	55.30	63.50 +0.13	5.99



ORDER DATA

SOCKET CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
09	PCB clip / Hex bolt	302 A 10779 X
15	PCB clip / Hex bolt	302 A 10789 X
25	PCB clip / Hex bolt	302 A 10799 X
37	PCB clip / Hex bolt	302 A 10809 X

PLUG CONNECTOR		
No. of pos.	Mounting style 4-40 UNC	Part Number
09	PCB clip / Hex bolt	301 A 10679 X
15	PCB clip / Hex bolt	301 A 10689 X
25	PCB clip / Hex bolt	301 A 10699 X
37	PCB clip / Hex bolt	301 A 10709 X

PCB clip .122" / 3.1 ± .004" / 0.10 mm hole diameter and .063" / 1.6 mm circuit board thickness