


8U Wall-Mount Bracket for Small Switches and Patch Panels, Hinged

MODEL NUMBER: SRWO8UBRKT



8U wall-mount bracket houses 19 in. rack equipment up to 14.75 in. deep, such as network switches and patch panels.

Features

Wall-Mount Bracket Is the Ideal Alternative to a Full-Size Rack Cabinet If you don't have enough equipment to justify the purchase of a full-size rack or you don't have enough space for one, this SmartRack® bracket is the ideal alternative for your home office or small business. Made from heavy-duty laser-cut 14-gauge cold-rolled steel with a durable black powder-coated finish, this 8U wall-mount bracket easily attaches to the wall of your back office or closet with the included mounting screws.

Hinged Bracket Supports EIA-Standard 19 in. Rack Equipment The SRWO8UBRKT houses 8U of compatible 19-inch rack components, including EIA-compliant switches and patch panels by any manufacturer, up to 14.75 inches deep. The 8U wall-mount bracket is hinged to allow open, unrestricted access to equipment and cabling from either the left or right side. Maximum load capacity is 35 pounds (15.9 kg)

Rear Cutout Eases Cable Installations The wall-mount bracket features an open cutout in the rear that allows for cable feeds through the wall to streamline installations and reduce cable clutter. The laser-cut metal bracket's surfaces and edges are smooth to reduce wear on cable jackets and patch panel equipment.

Easy Mounting with the Included Hardware Rear keyhole mounting slots are 16 inches apart to align with standard wall-stud placement. Stamped horizontal reinforcement ribs on the back of the bracket provided extra stability. The 8U wall-mount bracket comes with mounting screws for installing the bracket and rack equipment.

5-Year Warranty and Environmentally Responsible Design The SRWO8UBRKT comes with a 5-year warranty. It's manufactured in compliance with strict RoHS specifications.

Highlights

- Ideal for home office or small business with no floor space for full-size rack cabinet
- Steel construction with smooth laser-cut edges that won't damage cable jackets
- Supports universal mounting for left- or right-hinging to allow easy cable access
- Keyhole mounting slots spaced 16 in. apart to match standard wall-stud placement
- Includes hardware for immediate mounting of bracket and equipment

Applications

- Mounting standard 19 in. rack equipment in a closet or back room too small to contain a full-size rack
- Mounting 8U of patch panels and network switches that don't need to be secured in a rack cabinet

Package Includes

- SRWO8UBRKT 8U Wall-Mount Bracket for Small Switches and Patch Panels, Hinged
- (20) 12-24 mounting screws
- Assembly instruction sheet

Specifications

OVERVIEW	
UPC Code	037332205629



Powering Business Worldwide

TRIPP LITE
SERIES

Device Compatibility	Patch Panel
Rack Type	Bracket
Accessory Type	Mounting Accessories
PHYSICAL	
Color	Black
Rack Height	8U
Rack Depth	Shallow
Maximum Device Depth (cm)	38.10
Maximum Device Depth (in.)	15
Maximum Device Depth (mm)	381
Shipping Dimensions (hwd / in.)	3.94 x 21.46 x 17.13
Shipping Dimensions (hwd / cm)	10.01 x 54.51 x 43.51
Shipping Weight (lbs.)	18.18
Shipping Weight (kg)	8.25
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Dimensions (hwd / cm)	35.56 x 50.04 x 38.1
Unit Weight (lbs.)	11.00
Unit Weight (kg)	4.99
Weight Capacity - Stationary (kg)	16
Weight Capacity - Stationary (lbs.)	35
Number of Vertical Mounting Rails	2
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Built-in Cable Management	No
Extra Wide	No
Pre-Installed Casters	No
STANDARDS & COMPLIANCE	
Product Certifications	IEC 60297-3
Product Compliance	RoHS; EIA/ECA-310-E
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	5-year limited warranty



Powering Business Worldwide

TRIPP LITE
SERIES

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.