



Part Number : 1301080144

Series Number : 130108

Product Category : Lamps and Lights

Product Description : Super-Safeway 40W
Fluorescent Hand Lamp with 18/3 SJTW, Cord
Length 7.62m (25.0')

Status : Active

Engineering Number : 1097-3

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108

Description	Super-Safeway 40W Fluorescent Hand Lamp with 18/3 SJTW, Cord Length 7.62m (25.0')
NEMA Configuration	NEMA 5-15
Product Family	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678861254

Agency

CSA	LR85374
-----	---------

Electrical

Lamp Wattage - Maximum	40W
Lumens	2970
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	76.20mm (3.000")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	57.15mm (2.250")
Lamp Type	PL-L 40/41
Length	798.83mm (31.450")
Material - Globe	Clear Polycarbonate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Net Weight	1.000/g
Outlet	None
Packaging Type	Carton

This document was generated on Aug 31, 2024