



Part Number : [1210130006](#)

Product Description : mPm DIN Base

Series Number : 121013

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : B000107


Documents and Resources

Drawings

[1210130006_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:91481b7a-f62f-438b-b773-0d9984c78355
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)

[Additional Product Compliance Information](#)

[CE - Declaration of Conformity](#)

[UKCA - Declaration of Conformity](#)

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	121013
Description	mPm DIN Base
IP Rating	IP65, IP67
Product Name	mPm
Type	Field Attachable Connector
UPC	883906695439

Electrical

Current - Maximum per Contact	N/A
Voltage - Maximum	N/A

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	4.125/g
Orientation	N/A
Poles	N/A

Temperature Range - Operating	N/A
Wire Size (AWG)	N/A

This document was generated on May 16, 2026