RED INDICATES ORIGINAL

TABLE 1					
DASH NO	CABLES ACCOMMODATED	A HEX	B DIM	C MAX	ASSEMBLE PER
-201	M17/176-00002	.344	.030	1.80	TAI-168
-202	TWC-78-1				
-203	TWC-124-1A				
-204	10602,RAYCHEM				
-205	TWAC-78-1F2				
-206	7826D0130,RAYCHEM				
-207	83310,BELDEN				
-208	202-3927,MICRODOT				
-209	202-3942,MICRODOT				
-210	8451,BELDEN				
-211	202-3934,MICRODOT			1.55	TAI-138
-212	2524E0114,RAYCHEM				
-213	TWC-78-2				
-214	TWC-124-2				
-215	BL982,TIMES				
-216	BL1242,TIMES				
-217	GC875TM24H,GRUMMAN			1.80	TAI-166
-218	EOP221888,RAYCHEM				
-219	252601114,RAYCHEM				
-220	GC875RR1,GRUMMAN				
-221	10614,RAYCHEM				
-222	10613,RAYCHEM				
-223	HMS2-1149,HUGHES				
-301	GC875GC1,GRUMMAN				
-302	GC875GB1,GRUMMAN				
-303	7528A5314 RAYCHEM				
-304					
-305	M17/177-00001 THERMATICS				
-306	TRC-50-2 M17/134-00002				TAI-218
-307	TRC-7S-1				TAI-168
-308	TRC-7S-2				TAI-218
-309	TRC-50-1				TAI-168


TABLE 2 POLARIZATION CHART					
DASH NO	KEYING LETTER	D DEGREES	E DEGREES	F DEGREES	COLOR BAND
-1	T	100°	150°	110°	RED
-2	U	120°	130°	110°	ORANGE
-3	V	115°	130°	115°	YELLOW
-4	W	125°	110°	125°	GREEN
-5	X	130°	100°	130°	BLUE
-6	Y	110°	140°	110°	VIOLET
-7	Z	100°	160°	100°	GRAY
-8	S	135°	135°	90°	WHITE
-9	NONE	120°	120°	120°	NONE


DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO TROMPETER ELECTRONICS INC. AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUREMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION.

REVISIONS					
REV	ECO	DESCRIPTION	DWN	APPROVED	DATE
U	12815	CHANGED BOM ON -307; SEE ECO	R L		4/28/99


3-0209 SH 1C

INCH	MM
.005	0.13
.010	0.25
.030	0.76
.344	8.74
.546	13.87
1.00	25.40
1.25	31.75
1.416	35.97
1.55	39.37
1.75	44.45
1.80	45.72





-202 SHOWN



RECOMMENDED HEX CRIMP SCALE: 2/1

6. FOR TOOL CRIMP CONNECTOR QUALIFIED TO MIL-C-49142, SEE DRAWING 3-0298 (CJ70MC)

5. EXAMPLE OF COMPLETE MODEL NO.

CJ70C T -201

BASIC MODEL NO
POLARIZATION LETTER NONE REQD FOR STD POLARIZATION (SEE TABLE 2)
DASH NO (TABLE 1)

4 1 SHRINKABLE STRAIN RELIEF AND/OR SHRINKABLE SEALING SLEEVE SUPPLIED LOOSE AS FOLLOWS:

a. CABLE GROUPS -201 THROUGH -210, -217 THROUGH -303, -305, -307 & -309

1 SHRINKABLE STRAIN RELIEF (1.00 LONG)
1 SHRINKABLE SEALING SLEEVE (1.25 LONG)

b. CABLE GROUPS -211 THROUGH -216, -305 & -308

1 SHRINKABLE STRAIN RELIEF (1.75 LONG)

3. 3-LUG CONCENTRIC TWINAX/TRIAX TRB, FULL CRIMP CABLE RECEPTACLE

2. FINISH: TFS-1A (NICKEL)

1. ALL DIMENSIONS ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ± .005 .XXX ± .005 .XXXX± ANGLES±	TROMPETER RF connectivity	CJ70C	
DWN R.L. 4/23/99	MATERIAL	CODE IDENT 14949	DRAWING NO. 3-0209 REV U
CHK			
ENGR			
APPR	SCALE 4/1	DATE 11/11/88	SHEET 1C
NEXT ASSY			

Downloaded from Arrow.com.

Please read our datasheet & drawing disclaimer here.