
THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST
–	–

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	RELEASED	14.JUN'13	SH	HG
	A1	REVISED(ECR-15-015779)	28.OCT'15	SH	HG
	B	REVISED(ECR-16-010397)	19.JUL'16	SH	KT



3D VIEW
SCALE 1:1







TABLE 1


TYPE	P/N	SQ
.025TH	2005098-1	0.22
	2005154-1	0.3~0.5
.060	2109005-1	0.22~0.3
	2109005-2	0.5~0.75
	2109005-3	0.85~1.25
.110 (MCP)	2-964292-1	0.35~0.5
	2-964294-1	>0.5~1.0
	2-964296-1	1.25~2.5
	1-,2-,3-968946-1	>2.5~3.0








SECTION A-A





NOTE

1. GENERAL TOLERANCE: ±0.3, ±3°
2. RETAINER IS PRE-LOCKING
3. APPLICABLE TERMINAL: SEE TABLE
4. APPLICABLE CLIP : P/N :1-1897255-2
5. MATING P/N : 2188391

A1

DESCRIPTION	HYB 30P CAP ASS'Y	HYB 30P CAP ASS'Y
ASS'Y P/N	2188394-1	2188394-6

NO.	COLOR	MATERIAL	DESCRIPTION	Q'TY	
2	BLACK	PBT	DBL FOR 30P CAP ASS'Y	1	1
1	RED	PBT	025/060/110 30P HYB CAP HSG	–	1
	NATURAL	PBT	025/060/110 30P HYB CAP HSG	1	–

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±

MATERIAL –
FINISH –

DWN SH JANG
CHK KT JUNG
APVD KT LIM
PRODUCT SPEC –
APPLICATION SPEC –
WEIGHT –

TE Connectivity

NAME
–
025/060/110 HYB 30P CAP ASS'Y
–

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2188394	–

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 1 | REV B

Downloaded from Arrow.com.