





REV.	DATE	DESCRIPTION
NC	06/15/98	INITIAL RELEASE
A	07/20/05	UPDATE DRAWING FORMAT



RECOMMENDED
CABLE STRIPPING DIM'S

8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						07/20/05
6						CHECKED							
5	COVER	BRASS	NICKEL	1					PART DESCRIPTION				
4	FERRULE	BRASS	NICKEL	1					BNC R/A CRIMP PLUG (FOR BELDEN 9913, 9914, LMR400 CABLE)				
3	CONTACT PIN	BRASS	GOLD	1				PART NO.					
2	INSULATOR	TEFLON	NATURAL	1				112596					
1	BODY	BRASS	NICKEL	1				DWG. NO. 112596.DWG					
	DESCRIPTION	MATERIAL	FINISH	QTY			CAD FILE C:/112/112596.DWG		REV. A	SIZE A	SCALE NA		