



Part Number : [1301380116](#)

Product Description : Super-Safeway Cable Protector, 5-Channel, 0.90m (36.0") Length, Black with Safety Orange Flip Lid

Series Number : 130138

Status : Not Recommended For New Design

Product Category : Connector Accessories

Engineering Part Number : 610-MAIN



Documents and Resources

Drawings

[1301380116 sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Part Details

General

Status	Not Recommended For New Design
Category	Connector Accessories
Series	130138
Description	Super-Safeway Cable Protector, 5-Channel, 0.90m (36.0") Length, Black with Safety Orange Flip Lid
Component Type	Cable Protector
Product Name	Super-Safeway
UPC	78172550940

Physical

Circuits (Loaded)	N/A
Color - Resin	Black, Orange
Height	50.80mm
Length	1.0m
Material - Resin	Polyurethane
Packaging Type	Individual Carton
Temperature Range - Operating	-40° to +48°C
Width	0.50m

Mates With / Use With

Use with Part(s)

Description	Part Number
Super-Safeway Portable Power Distribution Box, Feed-Thru, (6) GFCI Protected NEMA 5-20 Duplex Receptacles, (1) NEMA L6-30 Locking Receptacle, NEMA Type 3R Rainproof	<u>1301380126</u>
Super-Safeway Portable Power Distribution Box, Feed-Thru, (6)	<u>1301380127</u>

GFCI Protected NEMA L5-20 Locking Single Receptacles, (1) NEMA L6-30 Locking Receptacle, NEMA Type 3R Rainproof	
--	--

This document was generated on Jun 09, 2026