



Part Number : [732510132](#)
Product Description : SMA Plug, Straight, Crimp,
RG-141, RG-303 and RG-58 Cable, Body Brass, Nickel
(Ni) Plated, 50 Ohms
Series Number : 73251
Status : Active
Product Category : RF / Coaxial Connectors
Engineering Part Number : 73251-0131



Documents and Resources

Drawings

[732510132 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

[Industry Documents](#)

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73251
Description	SMA Plug, Straight, Crimp, RG-141, RG-303 and RG-58 Cable, Body Brass, Nickel (Ni) Plated, 50 Ohms
Application	RF
Product Name	SMA
Style	Cable
Type	Subminiature
UPC	822348186525

Electrical

Frequency	18 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Crimp
Gender	Plug
Keying to Mating Part	N/A
Net Weight	3.918/g
Orientation	Straight

Packaging Type	Tray
Panel Mount	No
Panel Mount Method	N/A
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	RG-58, RG-141, RG-303, LMR-195

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Dec 29, 2025