


rote Kennader auf b1
red edge at b1




Verpackt in Tray *-tray packaging*
Verpackungseinheit 98 Stück - *packaging unit 98*



mit aufgesetzter Leitungsführung (Anlieferungszustand)
cable guide loose mounted (state at time of supply)





Leitungsführung verpresst
cable guide pressed on



siehe Verarbeitungsspezifikation SMC-IDC
according to Application Specification SMC-IDC

Detail X





Federleiste mit Schneidklemmanschluß Bauform B, BA 6
mit Verriegelungsmechanismus (angespritzt)

IDC Female Connector Type B with Locking Latches (formed on), BA 6

Dimension no.	Tolerances Dim. for Information ISO 8015 All Dimensions in mm	Scale 5:1	
		Material	
Customer drawing: This Drawing is a controlled Document.	Subject to modification without prior notice. Drawing will not be updated.	ERNI-SMC Female Connector B IDC Type 6 26p	
E1 / Index	11.10.2024 / Date	TE Connectivity	C-214346-E / C / A3
		Class SMCB	

Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung. Bei Abweichungen von dem englischen Original gilt das englische Original.
The german version of this drawing has been offered for convenience only and may deviate from the english original. In case of any deviation the English version shall prevail.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmustereintragung vorbehalten.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.

Downloaded from Arrow.com.