
PART NO.	ENGINEERING NO.	FINISHED LENGTH	
1300240207	DND09A-M010	1M [3FT 3 IN]	
1300240003	DND09A-M030	3M [9FT 10 IN]	
1300240210	DND09A-M060	6M [19FT 8 IN]	

B



MALE FACE VIEW

P1

1	DRAIN
2	RED
3	BLACK
4	WHITE
5	BLUE

WIRING DIAGRAM

NOTES:
1. MATERIAL: AS NOTED
2. FINISH: AS NOTED
3. ELECTRICAL:
   VOLTAGE RATING PER IEC 60664: 300V
   VOLTAGE RATING PER UL: 300V
   CURRENT: 4A
4. TEMP RATING: -20° TO +80°C
5. PROTECTION: IP67 (WHEN MATED)
6. COUPLING THREAD: 7/8"-16UN
7. UL RECOGNIZED FILE: E152210
   CSA CERTIFIED FILE: LR6837
8. ALL DIMENSIONS ARE FOR REFERENCE UNLESS TOLERANCED OR NOTED OTHERWISE

PART NUMBER LEGEND

DND09A-M010

CABLE LENGTH
M005= 0.5 METER
M010= 1 METER
M100= 10 METER

B

CABLE LENGTH TOLERANCES
<.3M [1FT]: +19mm-0 [+.75in-0]
.3 - .9M [1 - 3FT]: +44.5mm-0 [+1.75in-0]
.9 - 1.8M [3 - 6FT]: +55.6mm-0 [+2.19in-0]
1.8 - 3.7M [6 - 12FT: +88.9mm-0 [+3.50in-0]
3.7 - 7.3M [12 - 24FT]: +165.1mm-0 [+6.50in-0]
7.3-14.6M [24 - 48FT]: +317.5mm-0 [+12.50in-0]
14.6 - 30.5M [48-100FT]: +622.3mm-0 [+24.50in-0]
OVER 30M [100FT] +2% OF FINISHED LENGTH

ITEM	COMPONENT	MATERIAL	FINISH	
6	WRAP LABEL	VINYL	BLACK/YELLOW	
5	OVERMOLD	TPE	GRAY	B
4	COUPLING NUT	ZINC DIE CAST	BLACK-E-COAT	
3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL	
2	INSERT	TPE	BLACK	B
1	CABLE 22 AWG, DEVICENET	PVC	GRAY	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

FUNCTIONAL SYMBOLS
FA=0
FC=0
FP=0
DIVISIONAL SYMBOLS

DIMENSION UNITS: INCH/MM
SCALE: NTS

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	±----	±----
3 PLACES	±----	±----
2 PLACES	±----	±----
1 PLACE	±----	±----
0 PLACES	±----	±----
ANGULAR TOL ± ---- °		

DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS

CURRENT REV DESC: ITEM #2 & #5 WERE PVC. ADDED CABLE DIA & TOL CHART. MODIFIED PN CHART

EC NO: 720800
DRWN: ABENJAMINLW 2022/06/23
CHK'D: RSTONE 2022/09/09
APPR: BWOODMAN 2022/09/09

INITIAL REVISION:
DRWN: EBRACKEN 2013/06/18
APPR: BWOODMAN 2013/10/07

THIRD ANGLE PROJECTION | DRAWING: C-SIZE | SERIES: 130024

molex

MINI-CHANGE DEVICENET, A SIZE
5 POLE, MALE, 90DEG, SINGLE KEY,
#22/4 AWG

PRODUCT CUSTOMER DRAWING

DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
SD-130024-017	PSD	001	B

MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
SEE CHART	GENERAL MARKET	1 OF 1

DOCUMENT STATUS	P1	RELEASE DATE	2022/09/09 18:07:57

Downloaded from Arrow.com.