

Specifications



Photo is representative



Eaton UP0.4C-330-R

Eaton UP0.4C inductor, Inductance 33.0 μ H, 0.4 A Irms, 0.63 A Isat, 560 m Ω DCR

General specifications

PRODUCT NAME	Eaton 0.4C inductor
CATALOG NUMBER	UP0.4C-330-R
UPC	051712894036
EAN	5027590117760
PRODUCT LENGTH/DEPTH	0.26 in
PRODUCT HEIGHT	0.115 in
PRODUCT WIDTH	0.175 in
PRODUCT WEIGHT	0.0003 lb
COMPLIANCES	RoHS Compliant
GLOBAL CATALOG	UP0.4C-330-R

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.4 A
ISAT	0.63 A
PACKAGE QUANTITY	2500
MATERIAL	Ferrite
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	560 mΩ
SERIES	UP0.4C

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton UP04C unshielded drum core power inductors data sheet](#)

[Eaton Specification Sheet - UP0.4C-330-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

