

## Technical data sheet

Article number:  
151-02606

**CDC22S40.5M10**

<b>Material</b>	Polyamide 6.6 (PA66)
<b>Colour</b>	Black (BK)
<b>Bundle Ø max.</b>	22.0 mm
<b>Fixation Method</b>	screwable
<b>Flammability</b>	UL 94 V2
<b>for Hole Ø (FH)</b>	10.6 mm
<b>Height (H)</b>	72.8 mm
<b>Length (L)</b>	72.7 mm
<b>Mounting Screw Type</b>	M10 Screw
<b>Operating Temperature</b>	-40 °C to +105 °C
<b>Package Content</b>	500 pcs.
<b>Package Content packed in</b>	carton
<b>ROHS compliant</b>	Yes
<b>Width (W)</b>	23.0 mm

RoHS 