



Pneumatic Tensioning Tool with Plastic Housing

MK7P up to 4.8 mm strap width

The MK7P pneumatic bundling tool sets a new benchmark for the rational application of ties in the industrial production process. Improved compressed air supply moves the tensioning piston faster than in comparable tools.

Features and Benefits

- Pneumatic tensioning tool
- Light glass-fibre-reinforced housing
- For cable ties up to 4.8 mm width
- For consistent tensioning and automatically flush cutting
- Infinitely adjustable tension force
- High application speed



MK7P.



The easy to use quick-set-knob.

Air Supply	Non oiled / oiled
Air Pressure (min.)	3 Bar
Air Pressure (max.)	6 Bar
Hose Internal Diameter	4.0 mm
L x H x W	approx. 220 x 170 x 40 mm
Specifications	CE, GS

RoHS

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
MK7P	4.8	1.5	0.43 kg	110-07100
SP compressed air hose	-	-	0.35 kg	110-30002
SP MK7P replacement blade	-	-	0.01 kg	110-07111
SP lock cap tensioning knob	-	-	0.01 kg	110-07200

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.