


REV.	DATE	DESCRIPTION
NC	01/22/07	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"	APPROVALS		DATE		Amphenol Connex					
7						DRAWN	G.R.S.	01/22/07							
6						CHECKED			PART DESCRIPTION 1.0/2.3 PCB BULKHEAD JACK (SHORT BODY)						
5						ISSUED									
4	SPANNER NUT	BRASS	NICKEL	1		SHEET	1 OF 1			PART NO. 282124–75					
3	CONTACT PIN	BER. COPPER	GOLD	1											
2	INSULATOR	TEFLON	NATURAL	1						DWG. NO. 282124–75.DWG					
1	BODY	BRASS	GOLD	1											
DESCRIPTION MATERIAL FINISH QTY					DO NOT SCALE DRAWING	CAD FILE		C:/282/282124–75.DWG		REV.	NC	SIZE	A	SCALE	NA