



✓ Active

TE CONNECTIVITY
B140AL=RELAY

B140AL
TE Internal Number: 1616510-1

Not EU RoHS or ELV Compliant
Find Compliant Alternatives

Contact Arrangement **3PDT-NO**

Contact Current Rating(A) **50**

Coil Voltage (Max)(VDC) **28**

Coil Termination **8-32 UNC-2A Stud**

Coil Voltage Rating(VDC) **18 – 28**
[See All Features](#)

North America ▼

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION



SAVE TO LIST



CHECK FOR TOOLING



FIND SIMILAR PRODUCTS



DOCUMENTATIONFEATURES

Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Product Classification	Relays - Contactors
Product Type	Contactactor
Terminal Configuration	10-32 UNF-2A Stud
Contactactor Type	Sealed
Product Category	Electromechanical Relays

Electrical Characteristics

Coil Voltage (Max)(VDC)	28
Coil Voltage Rating(VDC)	18 – 28
Actuating System	DC

Contact Features

Contact Arrangement	3PDT-NO
Contact Current Rating(A)	50
Number of Poles	3

Termination Features

Coil Termination	8-32 UNC-2A Stud
------------------	------------------

Mechanical Attachment

Mounting Type	Chassis
---------------	---------

Product Compliance

[Statement of Compliance](#)
PDF
[VIEW ALL PRODUCT COMPLIANCE](#)

COMPATIBLE

No compatible products found for B140AL