

Power It! 7-Outlet Power Strip, 12 ft. (3.66 m) Cord, Black Housing

MODEL NUMBER: PS712B



Highlights

- 7 outlets
- 12-ft. (3.66 m) power cord
- Illuminated on/off switch
- 15 amp circuit breaker
- Keyhold mounting slots

Package Includes

- PS712B Power Strip
- Instruction manual and warranty information

Description

This PS712B power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. PS712B offers seven total outlets and a 12-foot power cord. Attractive black housing with keyhole mounting slots and one designated transformer plug outlet. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket.

Features

- 7 outlets / 12-ft. (3.66 m) cord
- Attractive black housing
- EMI/RFI noise filtering
- Can accommodate 1 transformer without blocking remaining outlets
- Keyhole supports for wall mounting

Specifications

OVERVIEW	
UPC Code	037332175212
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
Input Plug Type	NEMA 5-15P



Powering Business Worldwide

TRIPP LITE
SERIES

Input Cord Length (ft.)	12
Right-Angle Plug	No
Input Cord Length (m)	3.66
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(7) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Outlet Orientation	Single row
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2 position red illuminated on/off power switch
DATALINE SURGE SUPPRESSION	
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Color	Black
Material of Construction	Plastic
Power Cord Color	Black
Housing Color	Black
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between slots = 151mm; Distance between slot height = 24mm
Outlets Measurement (Center to Center)	Distance between standard outlets = 1.14 in.; Distance between last standard outlet and transformer outlet = 1.29 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.50 x 4.90 x 13.80
Shipping Dimensions (hwd / cm)	6.35 x 12.45 x 35.05
Shipping Weight (lbs.)	1.90
Shipping Weight (kg)	0.86
Unit Dimensions (hwd / in.)	1.480 x 2.050 x 11.690
Unit Dimensions (hwd / cm)	3.35 x 5.21 x 29.69
Unit Weight (lbs.)	1.76



Powering Business Worldwide

TRIPP LITE
SERIES

Unit Weight (kg)	0.80
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; NOM (Mexico); UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.