





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/11/08	
A		REDRAWN	11/18/10	



SECTION C-C

SPECIFICATIONS:

Material: Phosphor Bronze

Plating: Tin Plated

Electrical:

Voltage rating: 100 VAC/DC max

Current rating: 1 Amp max

Contact Resistance: 20 mOhms Max.

Dielectric withstanding voltage: 500 VAC for 1 minute

Mechanical:

Wire Range: 28-32 AWG.

Insulation Range: 0.90mm Max.

Packaging: Chain Reel, 15,000 pcs / reel

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES
.X ± .10 ØXX ± .10
.XX ± .020 ØXXX ± .015
.XXX ± .015 ØXXXX ± .010
APPROVALS
DATE

ADAM TECH
909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710
1.25mm TERMINAL FOR 125CH-D
CRIMP HOUSING

DRAWN	SS	11/11/08	SIZE	PART NO.	125CTD-R	REV.	A
CHECKED			X				
APPROVED			REF:	S00723T	SCALE: NTS	SHEET 1 OF 1	