


BC25, Copper Deadend Clamp, For Guy Wire, 1/0 Str, 3/8"

By Burndy
Catalog # [BC25](#)



Copper Deadend Clamp for Guy Wire, 1/0 Stranded, 3/8" Guy Wire, Supplied with silicon bronze U-bolt, nuts, and washers

Features

- Supplied with silicon bronze U-bolt, nuts and washers
- Saddle is made of high strength, corrosion resistant copper alloy

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	EX
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

Configuration

Connector Type	Deadend
----------------	---------

Dimensions

Dimension - Width inch	3.75 in
Package Length	0.000 in
Dimension - Width mm	95 mm
Package Width	0.000 in
Dimension - B Length fraction	1-3/8 in
Package Weight	0.000 lb.

Dimension - B Length inch	0.625 in
Dimension - L Length Overall mm	35 mm
Dimension - Pad Width inch	0.88 in
Dimension - Pin Diameter fraction	3/8 in
Dimension - Pin Diameter inch	0.38 in
Dimension - Height inch	2 in
Package Height	0.000 in
Dimension - Height mm	50.8 mm
Dimension - Length Overall inch	1.375 in
Dimension - Width fraction	1-3/4 in

General

Plated	N
Prefilled Oxide Inhibitor	N
UPC 14 Digit GTIN	00781810805428
Material	Copper Alloy
Plating Type	Unplated
UPC	781810805428

Logistics

Minimum Pack Quantity	26
Carton Quantity	25
Pallet Quantity	5250

Product Assets

[Catalog \[English\]](#)