

Part Number : [936011020](#)

Product Description : Heavy-Duty Standard (STD)
Single Lever Hood, Polyamide, with 2 Pegs, Side Entry,
without Cable Gland, Size «32x13», Pg21 Thread, Black

Series Number : 93601

Status : Active

Product Category : Heavy-Duty Connectors


Engineering Part Number : 7808.6643.1



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Single Lever Hood, Polyamide, with 2 Pegs, Side Entry, without Cable Gland, Size «32x13», Pg21 Thread, Black
Component Type	Single Lever Hood
IP Rating	IP66, IP67
Product Name	Heavy-Duty Connectors
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191865874

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Cable Diameter	11.00-18.00mm
Component Size	«32X13»
Entry Location	Side
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Polyamide

Material - Peg	Polyamide
Net Weight	25.000/g
Number of Pegs	2
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size «32x13» S-QD Inserts and 11.00-18.00mm Cable Diameter (Pg21) Polyamide Cable Gland

This document was generated on Jun 11, 2026