USB 2.0 Adapter Cable - USB-C to USB Micro-B (M/F), 6-in. (15.24 cm)

MODEL NUMBER: **U040-06N-MIC-F**



Convert the USB Type-C (USB-C) port on your device, tablet, laptop, ultrabook, or computer to a USB Micro-B Female port

Highlights

- Connect devices with a USB Micro-B port to the USB Type-C (USB-C) port on your tablet, laptop, ultrabook or computers
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in

System Requirements

- A device with a Micro-B connector
- A tablet, laptop, ultrabook or computer with an available USB Type-C (USB-C) port

Package Includes

- USB 2.0 Hi-Speed Adapter Cable, USB Type-C (USB-C) Male to USB Micro-B Female, 6-in.

Features

- 6-in. USB Type-C (USB-C) Male to USB Micro-B Female adapter cable
- Converts the USB Type-C port on your tablet, laptop, ultrabook, or computer to a USB Micro-B port, allowing for Micro-B devices to sync and charge
- USB Type-C connector is reversible, so there is no guessing on which way to plug it in
- Supports USB 2.0 data transfer rates up to 480Mbps
- Backward compatible with previous USB generations
- Gold plated contacts and molded ends provide a lifetime of use
- 30AWG Data Pair / 24AWG Power Pair

Specifications

OVERVIEW	
UPC Code	037332189226
Technology	USB 2.0 (High Speed)
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	MICRO-USB B (FEMALE)
Connector Plating	Nickel
Contact Plating	Gold

Downloaded from Arrow.com.

Connector Style	Straight
PHYSICAL	
Material of Construction	PVC
Cable Jacket Color	Black
Cable Jacket Rating	VW-1
Cable Outer Diameter (OD)	3.0MM
Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	-4° to 185°F (-20° to 85°C)
Relative Humidity	10% to 85%, Non-Condensing
FEATURES & SPECIFICATIONS	
USB Specification	USB 2.0 (up to 480 Mbps)
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.