
Downloaded from Arrow.com.

MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01) PART NO.	MATERIAL: NYLON 6/6 UL 94 V-0 (RMS-19) PART NO.	"A"	ADHESIVE TAPE
MWSSEB-1-01A-RT	MWSSEB-1-19A-RT	3/8 (9.5)	RMS-15
MWSSEBE-1-01	MWSSEBE-1-19	1/2 (12.7)	W/O TAPE
MWSSEBE-1-01A	MWSSEBE-1-19A		RMS-15



NOTES:
1. COLOR: NATURAL.
2. ACRYLIC ADHESIVE TAPE, WHITE LINER (SEE TABLE).

REV	DESCRIPTION	ENGR DATE
L	CHANGED PART NUMBER, ECN # 1364	DZ 06.20.12
K	SEE CO 200405 FOR CHANGES	SK 07.31.09
J	SEE CO 200003 FOR CHANGES	SK 09.06.07
I	SEE ECN #1103. FOR CHANGES	SK 12.01.05
H	SEE ECN #1004 FOR CHANGES	SK 05.13.05
G	SEE ECN #747 FOR CHANGES	SM 01.21.04
F	SEE ECN #544 FOR CHANGES	SM 12.18.02
E	UPDATED PRINT AND ADDED NOTE 3.	SM 03.13.02
D	CHANGED FILE NO. AND TITLE BLOCK	SM 05.29.01
C	CONVERTED TO ACAD	PB 05.12.95
B	1/4 (6.4) MAX. REDIMENSIONED	RS 08.17.92
A	ADDED PART NO. MWSSEBE-1-01A-RT	RS 05.04.92

TITLE: MICRO WIRE SADDLE, SIDE ENTRY, ON BASE

DWG IN IN (MM)

TOLERANCES UNLESS NOTED
.XX=±.010
.XXX=±.005
FRAC=±1/64
ANG=±1°

FILE # MWSSEB
MAT'L: SEE NOTES
RE: RICHCO, INC.

DWN: P.B. APP:
DT: 05-12-95 DT:

RICHCO INC.
PO BOX 804238,CHICAGO,60680
(773) 539-4060

FINAL

PART # SEE NOTES

PRINT TYPE CA