


Expandable Braided Polyester Sleeving

Features

- Allows Flexibility while Providing Secure Bundling
- Easy to Install, Lightweight and Flexible
- Bundles Cables and Organizes Wires for a Professional Look
- 16.4 foot (5 meter) Lengths
- Material: Flame Retardant Polyethylene Terephthalate (PET)
- Working Temperature Range: -50° to $+150^{\circ}\text{C}$ (-58° to $+302^{\circ}\text{F}$)
- Flammability: Self-Extinguishing, met UL1441 VW-1
- Melting Point: $+250^{\circ}\text{C} \pm 5^{\circ}$ ($+482^{\circ}\text{F} \pm 5^{\circ}$)
- Specific Gravity @ $+73^{\circ}\text{F}$ ($+23^{\circ}\text{C}$): 1.39
- Tensile Strength @ $+73^{\circ}\text{F}$ ($+23^{\circ}\text{C}$) PSI: 39.275
- Elongation: 30%
- Water Absorption: 0.08%

ES-01



Expandable Braided Polyester Sleeving

NTE Type No.	Size (inch)	Expandable Range, I to O (in. / mm)	Dia. of Monofilament*Strand (E)	Weight (g/100M)	Diag No.
04-ES-125	1/8"	.094 (2.4) – .252 (6.4)	0.25*1	220	ES-01
04-ES-250	1/4"	.126 (3.2) – .437 (11.1)	0.25*3	575	ES-01
04-ES-375	3/8"	.189 (4.8) – .626 (15.9)	0.25*3	910	ES-01
04-ES-500	1/2"	.252 (6.4) – .752 (19.1)	0.25*3	1100	ES-01
04-ES-750	3/4"	.500 (12.7) – 1.252 (31.8)	0.25*3	1410	ES-01
04-ES-1000	1"	.626 (15.9) – 1.500 (38.1)	0.25*3	1650	ES-01