

Isolation - Step Down (240VAC to 120VAC) 289 Series

Plug-In

Features



- Primary 240VAC, 50/60 Hz., Secondary 120VAC.
- Provides circuit isolation.
- Toroidal transformer for high isolation, low noise, light weight, cool operation and low profile.
- World wide applications, 50 or 60 Hz. operation, step down (240VAC to 120 VAC).
- Input (primary) connected to a 5 foot long cord & standard 250V 2 pole, 3 wire - North American plug (NEMA 6-15P).
- Output (secondary) connected to two standard - 3 wire grounded receptacles (NEMA 5-15R).
 - Receptacles have North American pins. See our **298G adaptor series** for international pinout adaptor plugs.
- Features include ventilated black steel case, rocker lighted on-off switch & circuit breaker protected output.
- North American Mark of Safety - C UL & UL listed (File #E211544).
- Indoor use only.
- **Remember** - These units do NOT convert line frequency.
- **Note about Inrush Current:**
Due to the superior magnetic properties of Toroidal transformers they will be susceptible to high magnetizing current when initially energized, only limited by the low DC resistance of the primary winding. Depending on where you are in the AC cycle when the transformer is energized dictates the chances of overloading the supply circuit. This is why the transformer may sometimes energize without a problem and other times it will blow the fuse or trip the circuit breaker. The duration of this overload is rarely longer than a half of a cycle. Therefore, you should consider using a slow-blow fuse, time delayed circuit breaker or other form of soft start circuitry for the supply line when using these high efficient Toroidal transformers.

Accessories

- International Grounded Adaptor Plugs

Part No.	Capacity (VA)	# of Outlets	Width	Dimensions	
				Height	Length
289CT	250	2	6.00	4.00	8.25
289DT	500	2	6.00	4.00	9.00
289ET	750	2	7.50	5.00	10.25
289FT	1000	2	7.50	5.00	10.25
289GT	1500	2	9.00	5.00	12.50

