



+ FIBER OPTICS

FIBER OPTIC PATCH CABLE ASSEMBLIES



✓ Active

TE CONNECTIVITY (TE)
C/A,F/O,2F I/O MM50 OM3,SCLC DPX
FullAXS | DPU , Fiber Optic

1-2064915-3
TE Internal Number: 1-2064915-3

EU RoHS Compliant with Exemptions
EU ELV Compliant with Exemptions

Cable Type OFNR
Fiber Diameter (µm) 50/125
Outside Cable Diameter 7.5 mm [.295 in]
Number of Fibers 2
Connector Color (End A) Black

↓ PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

CABLE ASSEMBLY, FIBER OPTIC, 50/125, OM3, 2 FIBER BREAKOUT CABLE, SEALED CIRCULAR LC DUPLEX (ODVA), BOTH ENDS

PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features

Cable Type OFNR
Mode Multimode
Connector Type (End A) LC ODVA
Connector Type (End B) LC ODVA
Connector Style (End A) Duplex
Connector Style (End B) Duplex
Fiber Type OM3
Fiber Channel No
Product Type Cable Assembly
Cable Assembly Type LC Duplex to LC Duplex

Configuration Features

Number of Fibers 2
Cable Buffering Tight Buffer
Number of Connectors (End B) 2
Number of Connectors (End A) 2

Signal Characteristics

Insertion Loss B (Max) (dB) .55
Insertion Loss A (Max) (dB) .55

Body Features

Connector Color (End A) Black
Connector Color (End B) Black
Cable Color Black
Boot Type (Left) Standard
Boot Type (Right) Standard
Boot Color (Left) Black
Boot Color (Right) Black
Ferrule Material Ceramic

Dimensions

Fiber Diameter (μm) 50/125
Outside Cable Diameter 7.5 mm [.295 in]

Industry Standards

Flammability Rating OFNR (Riser) Jacket

Other

Cable Assembly Length (m) 13

PRODUCT COMPLIANCE

+

Statement of Compliance

Statement of Compliance
PDF

