

85134

[Products](#) > [Controls and Monitors](#) > [Operator Controls](#) > [Hour Meters](#) > [dc Hour Meters](#) > [85000 Series](#) > **85134**

Overview

Honeywell Quartz Plus dc Hour Meter, round opening, three screw flange mounting with deluxe black bezel, 0.25 bent blade termination, 100K hours, 12 Vdc to 60 Vdc operating voltage

[View More](#)



Technical Specifications

Product Type	Quartz + Hour Meter	Function	Hour Meter
Appearance	Round	Mounting	3 Screw
Voltage	12 Vdc to 60 Vdc	Bezel	Black
Hours	100K	Run Indicator	Yes
Logo Top	Honeywell Quartz	Logo Bottom	Hours

[View More](#)

View documents in:

English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 85134_highres_photo	Photo	English	3MB
 85134_lowres_photo	Photo	English	253KB
 Sensors and Switches in Front Loaders	Application Note	English	3MB
 True Time Stamp - Hour Meters	Case Study	English	345KB

[View More](#)

Product Features

- Custom CMOS inegrated circuit
- Indicates operating time in hours and tenths, plus has a running indicator
- Totally sealed
- Battery system voltages: 6, 12, 24, 36, 48 60, 72, and 80 Vdc
- UL, CSA

Applications

- Lawn tractors
- Garden tractors
- Farm equipment
- Gen sets
- Construction equipment
- Utility vehicles
- Industrial equipment
- Recreational vehicles
- Golf carts
- Aircraft

view all 85134 literature

view distributor inventory

sample request

email support

get support

email sales

find a distributor

email this page

- Medical equipment
- Office equipment

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

[English](#) ▼

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITEMAP](#)

[TERMS & CONDITIONS](#)

[COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.](#)