





CAV. NO.

POS. AND DIMENSIONS:

PIN	DIM.(mm)				PIN	DIM.(mm)			
	A	B	C	D		A	B	C	D
02	4.40	1.80	2.20		12	8.80	12.40	9.80	10.20
03	1.60	5.20	2.60	3.00	13	9.60	13.20	10.60	11.00
04	2.40	6.00	3.40	3.80	14	10.40	14.00	11.40	11.80
05	3.20	6.80	4.20	4.60	15	11.20	14.80	12.20	12.60
06	4.00	7.60	5.00	5.40	16	12.00	15.60	13.00	13.40
07	4.80	8.40	5.80	6.20	17	12.80	16.40	13.80	14.20
08	5.60	9.20	6.60	7.00	18	13.60	17.20	14.60	15.00
09	6.40	10.00	7.40	7.80	19	14.40	18.00	15.40	15.80
10	7.20	10.80	8.20	8.60	20	15.20	18.80	16.20	16.60
11	8.00	11.60	9.00	9.40					

NOTES:

- 1. MATERIAL(HALOGEN FREE): LCP, UL94V-0 (CREAM)
- 2. GLOW WIRE COMPATIBLE.
- 3. USE WITH: 10145493 CRIMP TERMINAL
- 3. MATE WITH HEADER: 10144041, 10144042
- 4. PRODUCT SPEC: GS-12-1444
- 5. PACKAGING SPEC: GS-14-2616
- 6. ORDERING CODE: 10145492-XXLF

PIN NO.

02~20

mat'l. code				surface		tolerance		projection		product family	
ISO 1302				ISO 406		ISO 1104				MINITEK	
tolerances unless otherwise specified				.0±.25		mm				0.8MM RECE HOUSING	
A				0°±x°		mm					
B				linear		.00±.15		scale 1:1			
TONY 2017-09-13				dr		TONY LENG		2017-09-13		dwg no	
engr Jason Wang				chr		L.Q. Lei		2019-05-09		sheet 1 of 1	
pppd TIM YAO				2019-05-09						size	
										A3	
										type	
										Product Customer Drawing	
						</					