




Part Number : [936060009](#)
Product Description : Gwconnect Modular
Power Interface, Germany + Italy Socket
Profile, 250V,10.0A-16.0A
Series Number : 93606
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Number : 2000.3013.0



NO IMAGE AVAILABLE

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Heavy-Duty Connectors
Series	93606
Description	Gwconnect Modular Power Interface, Germany + Italy Socket Profile, 250V,10.0A-16.0A
Component Type	Power Interface
Product Name	GWconnect
UPC	887191822044

Electrical

Current - Maximum per Contact	10.0A, 16.0A
Voltage - Maximum	250V

Physical

Housing Color	Black
Net Weight	60.300/g
Packaging Type	Bag

Use with Part(s)

Description	Part Number
Use With	Size 32A «66x40» Bulkhead Housings.

This document was generated on Mar 09, 2025