



[Home](#) / [Power Discretes & Modules](#) / [Diode and Rectifier Devices](#) / [UES1305HR2 \(#16658\)](#)

UES1305HR2 (#16658)

Product Status

In Production

[Overview](#) [Resources](#) [Diagrams](#) [Ordering](#) [Support](#)

Package

ESD Bag

Carrier:

Electrical Rating	Symbol	Min	Typ	Max	Unit
Forward Voltage (V)	V _F			1	V
Reverse Current (μA)	I _R			20	μA
Reverse Recovery Time	t _{rr}			50	ns

Maximum Electrical Rating	Symbol	Min	Typ	Max	Unit
Output Current (A)	I _{OUT}			5	A
Reverse Breakdown Voltage	V _{BR}			300	V

Alphanumeric Parameter	Value
Rectifier Type	Ultra Fast (trr < 100 ns)
Quality Level	-

This part can be found in the following product categories:

- [Power Discretes & Modules](#) ▶ [Diode and Rectifier Devices](#)