

May not be suitable for all medical and aerospace applications.

Specifications: Contact Mallory Sonalert to discuss your application.

Resonant Frequency (Hz)	4000 ± 500
Operating Voltage (V _{p-p} /max)	20
Rated Voltage (V _{p-p})	9.0
Current Consumption (mA/max)	7.0 at Rated Voltage
Sound Pressure Level (dB/min)	85 at 10cm at Rated voltage
Capacitance (pF)	12,000 ±30% at 120Hz
Operating Temperature (°C)	-20 ~ +60
Storage Temperature (°C)	-30 ~ +70
Housing	PBT1200 UL94HB plastic resin (Color: Black)
Lead Pins	Tin Plated Brass
Weight (Grams)	1.5
Condition by wave soldering (°C)	260 ±5 / within 5 sec
Condition by hand soldering (°C)	350 ±20 / within 5 sec
Options	For other options contact factory

NO CIRCUITRY

Dimensions: (units: mm)

ROHS Compliant

