NEUTRIK



NADB9MF-B

9 pole D-SUB feedthrough, male to female, black D-shape housing

Features & Benefits

- Ideal for audio networking and integration of equipment into video systems
- Universally accepted standard D-shape housing

Technical Information

Product	
Title	NADB9MF-B
Gender	male

Electrical	
Contact resistance	30 mΩ
Insulation resistance	> 5 GΩ
Number of electronical contacts	9
Rated current per contact	3 A
Rated voltage	50 V ac
Dielectric strength	> 0.5 kVac

All rights reserved / 10.05.2026

Downloaded from Arrow.com.

NEUTRIK

Mechanical	
Panel thickness	4 mm
Wiresize	
Wiring	Feedthrough
Mounting direction	Front mounting
Chassis shape	D

Material	
Contact plating	Au
Contacts	Brass (Pb-free)
Insert	Steel , tin plated, PBT
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black chromium

Environmental	
Flammability	UL 94-V0
Temperature range	-25 °C to +85 °C

All rights reserved / 10.05.2026

Downloaded from Arrow.com.