Part Number : 395430004
Product Description : 5.00mm Pitch Eurostyle Vertical Fixed Mount PCB Terminal Block, with Screw Pressure Clamp, 4 Circuits
Series Number : 39543
Status : Active
Product Category : Terminal Blocks and Barrier Strip



Documents and Resources

Drawings

395430004_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Terminal Blocks and Barrier Strip
Series	39543
Description	5.00mm Pitch Eurostyle Vertical Fixed Mount PCB Terminal Block, with Screw Pressure Clamp, 4 Circuits
Application	Wire-to-Board
Component Type	One Piece
Product Name	Eurostyle Fixed Mount
Type	PCB Terminal Blocks and Connectors
UPC	822350536035

Agency

UL	E48521

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	300V

Physical

Circuits (Loaded)	4
Circuits (maximum)	4

Downloaded from Arrow.com.

Color - Resin	Black
Entry Angle	Horizontal
Lock to Mating Part	No
Number of Rows	1
Orientation	Vertical
Panel Mount	No
PCB Thickness - Recommended	2.50mm
PC Tail Length	3.60mm
Pitch - Mating Interface	5.00mm
Pitch - Termination Interface	5.00mm
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Wire Size (AWG)	14, 16, 18, 20, 22, 24
Wire Size mm^2	0.20-2.08

Solder Process Data

Max-Duration	5
Lead-Free Process Capability	WAVE
Max-Cycle	135
Max-Temp	260

Downloaded from Arrow.com.