

76079

Products > Switches > Pressure Switches > Standard Pressure Switches > 5000 Series > 76079

Overview

5000 Series pressure switch with standard terminal. These switches sense a change in the pressure, opening or closing an electrical circuit when the designated set point is reached. Honeywell S&C offers an impressive line of standard products, but our engineering expertise and understanding afford us the ability to modify existing parts or create an original component per a customer's specifications.


 view distributor inventory

 sample request

 email technical support

 start a chat
we're offline

 get support

 email sales

 find a distributor

 email this page

Feedback

Technical Specifications

Operating Pressure	250 psi	Product Type	Pressure Switch
Connector(s)	1/8-27 NPT	Contact	51 psi to 90 psi, ± 7 psi
Standard Factory Set Points	60 psi	Setting Range	
Circuitry	NO/NC, adjustable	Electrical Termination	1/4 in spade terminals
Proof Pressure	500 psi	Contact(s)	Silver alloy, gold plated
		Burst Pressure	1250 psi

[View More](#)View documents in:

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 HP, HE, MH, ME, LP, and LE Series Pressure Switches Datasheet	Datasheet	English	3MB
 Series 5000 Extended Duty Pressure Switch Datasheet	Datasheet	English	120KB
 Embedded Products in Hospital Applications	Brochure	English	5MB
 Honeywell Pressure Switches HP-HE-ME-LP-LE Series Applications	Application Note	English	1MB

[View More](#)

Product Features

- Stands up to extended duty applications
- Factory set, capable of field adjustment
- Direct acting blade - gold-plated contacts
- No dead band
- Kapton diaphragm for compatibility with a variety of fluids
- Various electrical connections and terminations
- Optional rubber boot

Applications

- Engine transmission
- Hydraulics and brakes
- Power steering
- Fuel pressure
- ABS brakes
- Cruise control
- Oxygen concentrators
- Dental air
- Embalming equipment
- Generators/compressors
- Pool/spa water pressure

NAVIGATION LINKS

[HOME PAGE](#)

[PRODUCTS](#)

[DISTRIBUTOR INVENTORY](#)

[INDUSTRIES](#)

[SUPPORT](#)

[NEWS & EVENTS](#)

[ABOUT US](#)

DISTRIBUTOR LINKS

[ECOM LOGIN](#)

[LEARN CENTER](#)

[REQUEST ACCESS TO ECOM](#)

[SALES/AD PORTAL LOGIN](#)

[SALES/AD PORTAL ACCESS REQUEST](#)

[SAMPLE REQUEST](#)

[SUPPLIER MICROSITE](#)

LANGUAGE

[English](#)

SOCIAL MEDIA



SITE INFORMATION

[PRIVACY STATEMENT](#)

[SITE MAP](#)

[TERMS & CONDITIONS](#)

This site uses cookies to simplify and improve your usage and experience of this website. Cookies are small text files stored on the device you are using to access this website. If you ignore this message and continue without changing your browser settings, we will assume that you are consenting to our use of cookies. For further information on our use of cookies, please see [Privacy Statement](#).

[Don't show this message again](#)