

Representative Image

Catalog No. L-14-50-0-C

Description: CABLE TIE 50LB 14 UV BLK 1-PC DIST

UPC No 728494912400

Home > Wire & Cable Management > Catamount > Cable ties

Standard Cable Tie, Weather and Ultraviolet Resistant for Indoor and Outdoor Applications, Black Color Nylon 6.6, Length of 371mm (14.6 Inches) for Bundle Diameter up to 76.2mm (3 Inches), Width of 4.6mm (0.18 Inches), Tensile Strength Rating of 222 Newtons (50 Pounds), Operating Temperature of -40 Degrees Celsius (-40 F) to 85 Degrees Celsius (185 F), UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, 100 Pack

Descriptors

Category	Cable ties
Type	UV Resistant Black
Application	Cable ties are primarily used to cinch wires and cables together to form a neat and organized bundle

Specifications

Material	Natural Polyamide (Nylon 6.6)
Color	Black
Lock Mechanism	Plastic Pawl
Tensile Strength	50 lb, 222 N

Classifications

Brand Name	Catamount

Dimensions

Width	0.18 in, 4.6 mm
Length	14.6 in, 371 mm
Thickness	0.05 in, 1.3 mm
Bundle Diameter	0.12 in - 4.02 in, 3 mm - 101.6 mm

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

by ABB

Downloaded from Arrow.com.