

Representative Image

Catalog No. RA18-6

Description: INS NYL RING TERM 22-16 BLT No6 RED

UPC No 786210803852

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Nylon Insulated Ring Terminal, Length 0.86 Inch, Width 0.26 Inch, Max Insulation 0.136, Bolt Hole #6, Wire Range #22-16 AWG, Color Red, Copper, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	Self-insulated with high dieletric-strength nylon sleeves. An inner bronze insulation grip sleeve lengthens the flexing radius of the conductor and eliminates conductor creep.

Specifications

Voltage Rating	600 V
Material	Copper
Color	Red

Classifications

Brand Name	Sta-Kon
Standard	UL E9809

Dimensions

Wire Size	22-16 AWG

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 253 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Ring shape
Insulation	PA
Colour insulation	Red
Reel packaging	N
AWG-range	22-16

Downloaded from Arrow.com.

ETIM	EC001052 Solderless copper terminals for copper conductors
Material	Copper
Surface protection	Tinned
Stud size (imperial)	6

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
CSA	4503	622302	N/A	N/A	N/A
CSA	7222	622302	N/A	N/A	N/A
UL	E9809	N/A	N/A	N/A	N/A

Downloaded from Arrow.com.