



Part Number : 936011375
Product Description : Heavy-Duty Standard (STD)
Double Locking Cover, Die-cast Aluminum, with 4 Pegs,
with Gasket, Size 10B «57x27», Grey
Series Number : 93601
Status : Active
Product Category : Heavy-Duty Connectors
Engineering Part Number : 7810.5120.0



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Heavy Duty Connectors
Series	93601
Description	Heavy-Duty Standard (STD) Double Locking Cover, Die-cast Aluminum, with 4 Pegs, with Gasket, Size 10B «57x27», Grey
Comments	With nylon wire tether line.
Component Type	Cover
IP Rating	IP66
Product Name	Heavy-Duty Connectors
Type	STD
UPC	887191887821

Agency

CSA	256883
UL	E249674

Electrical

Voltage - Maximum	500V
-------------------	------

Physical

Component Size	10B «57X27»
Cover Coating	Polyester Powder
Cover Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Cover	Die-cast Aluminum
Material - Peg	Stainless Steel
Net Weight	55.200/g
Number of Pegs	4

Packaging Type	Bag
----------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
Use With	Size 10B «57x27» Inserts with 4 Pegs

This document was generated on May 27, 2026