
Part Number : 351560300
Product Description : 3.96mm Pitch Wire-to-Board Housing, Positive Lock, Natural, 3 Circuits
Series Number : 35156
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

351560300_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

351560200-100.pdf

PK-35156-001-001.pdf

PS-35156-003-001.pdf

PS-35156-001-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	35156
Description	3.96mm Pitch Wire-to-Board Housing, Positive Lock, Natural, 3 Circuits
Application	Wire-to-Board
Component Type	Receptacle
Product Name	N/A
UPC	800754375764

Agency

CSA	LR19980
UL	E29179

Physical

Circuits (maximum)	3
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes

Downloaded from Arrow.com.

Material - Resin	Polyester
Net Weight	0.933/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Pitch - Termination Interface	3.96mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Solder Process Data

Lead-Free Process Capability	N/A

Mates With / Use With

Mates with Part(s)

Description	Part Number
3.96mm Pitch Vertical Headers	35313
7.92mm Pitch Vertical Headers	35328

Use with Part(s)

Description	Part Number
Mighty-SPOX Female Crimp Terminals	50217

Downloaded from Arrow.com.