

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0845100004

Status:

Active

Overview:

XRC (Extra Rugged Circular) Sealed Plugs and Receptacles

Description:

XRC Sealed Plug with Socket Insert, Shell Size 24, 31 Circuits, without Collar

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-84501-001-001 (PDF)

Packaging Specification PK-84501-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E152602
General	
Product Family	Crimp Housings
Series	84510
Application	Power, Wire-to-Wire
Comments	See Product Specification, See Product Specification
Overview	XRC (Extra Rugged Circular) Sealed Plugs and Receptacles
Product Name	XRC
UPC	883906514945
Physical	
Circuits (maximum)	31
Circuits Detail	31
Color - Resin	Black
Flammability	94V-0
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	59.420/g
Number of Rows	0
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	N/A
Pitch - Termination Interface	N/A
Temperature Range - Operating	-40° to +130°C
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-84501-001-001
Product Specification	PS-84501-001-001
Sales Drawing	SD-84510-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

84510 Series

Mates With

84511 Receptacle

Use With

84525 XRC Sealed Terminal Socket

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION