



Part Number : [1301370192](#)

Product Description : Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, F3 (3/4") Cord Grip Body, with Flip Lids for (2), NEMA 5-20 Duplex Receptacles

Series Number : 130137

Status : Active

Product Category : Power Distribution

Engineering Part Number : 3085-10



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Power Distribution
Series	130137
Description	Super-Safeway Multiple Outlet Box, Extended Depth, 2-Sided, F3 (3/4") Cord Grip Body, with Flip Lids for (2), NEMA 5-20 Duplex Receptacles
Enclosure Rating	N/A
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Multiple Outlet Box
UPC	78678875037

Agency

CSA	LR6837
UL	E46237

Electrical

Current - Maximum per Contact	N/A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	250V

Physical

Cord Diameter	11.10-19.05mm (.437-.750")
Cord Grip Body Size	F3 3/4"
Cord Length	N/A
Cord Type	N/A

Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable
Net Weight	820.547/g
Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on May 20, 2026