



CONNECTOR HOUSINGS



✓ Active

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**



TE CONNECTIVITY (TE)
POWER DBL LOCK CAP HSG F/H 2P(GWT)
[Power-Signal Double Lock](#) | [Power Double Lock](#)


5-179463-1
TE Internal Number: 5-179463-1

[Always EU RoHS/ELV Compliant](#)
Connector System **Wire-to-Wire**
Centerline **3.96 mm [.156 in]**

Number of Positions **2**

Number of Rows **1**

Housing Material **Nylon 6/6**



Product Drawings

[AMP POWER DOUBLE LOCK CONN. 3.96mm PITCH CAP HOUSING 2 Pos \(FREE HANGING\)](#)
PDF
English

CAD Files

[3D PDF](#)
PDF
3D

[Customer View Model](#)
2D_DXF.ZIP
English

[Customer View Model](#)
3D_IGS.ZIP
English

[Customer View Model](#)
3D_STP.ZIP
English

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Connector System	Wire-to-Wire
	Connector Style	Receptacle
	Sealed	No
	Product Type	Connector
	Connector Type	Housing
	Applies To	Wire/Cable
Configuration Features	Number of Positions	2
	Number of Rows	1
	Selectively Loaded	No
	Preloaded	No
Electrical Characteristics	Operating Voltage (VAC)	300
Body Features	Sealable	No
Contact Features	Contact Type	Tab
	Shunts/Shorting Bars	Without
	Multiple Contact Types	Without
Mechanical Attachment	Contact Retention	Without
Housing Features	Centerline	3.96 mm [.156 in]
	Housing Material	Nylon 6/6
	Housing Color	Natural
Dimensions	Height	26.1 mm [1.02 in]
	Width (mm)	9.4
Usage Conditions	Operating Temperature Range	-30 – 105 °C [-22 – 221 °F]
Operation/Application	Assembly Integration Feature	Without

Identification Marking	Circuit Identification Feature	Without
Industry Standards	CSA Certified	Yes
	CSA Rating	Certified
	Agency/Standard	CSA, UL
	CSA File Number	LR7189
Packaging Features	Packaging Quantity	300
	Packaging Method	Bag
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	

