Product Line

Single Pair Ethernet
ZConnect
Ceres
X-Lok
Accessory
Middle Size
Mini Size
Large Size
Standard Size
M Series
FLOS & FLOS+
Power
RBL
HS-Lok
NMEA 2000
Heavy Duty Shielded
RJ
USB
HDMI
DVI
Fiber Optic
RF
Cable Joiner
Cable Gland
Pressure Relief Vent
LED Light Guide
D-Sub





CAP-WAAMQMD1

- Operating Temperature: -40°C ~ +105°C
- Transmission Speed: N/A
- Shielded: Plastic, Non-shielded
- Jacket Material: N/A
- Certificate: N/A

You must login first for view the price

Quantity − 1 + Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type ▾ Search



SPF. X-Lok. Plastic...
AD-02BMMM-OL8P01
-20°C ~ +80°C



SPF. X-Lok. Plastic...
AD-02BMMM-OL8P02
-20°C ~ +80°C



SPF. X-Lok. Plastic...
AD-02BMMM-OL8P03
-20°C ~ +80°C



SPF. X-Lok. Plastic...
AD-02BMMM-OL8P04
-20°C ~ +80°C

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current N/A	Connector Type Waterproof Cap
Shielded Plastic, Non-shielded	No. of Contacts N/A
Connector Gender Male	Backshell N/A
Mating Style Push Lock	IP Rating N/A
Assembly Style With Fish Line	

More Options

People Also Bought

Downloaded from Arrow.com.