

# SEK CAB FLAT COLOR AWG28/7 40P 30,48m



Image is for illustration purposes only. Please refer to product description.

Part number	09 18 040 7005
Specification	SEK CAB FLAT COLOR AWG28/7 40P 30,48m
HARTING eCatalogue	<a href="https://harting.com/09180407005">https://harting.com/09180407005</a>

## Identification

Category	System cabling
Element	Bulk cables
Specification	Not assembled
Type of cable	Copper cable (flat)

## Version

Cable length	30.48 m
Number of cores	40
Core structure	AWG 28/7

## Technical characteristics

Limiting temperature	-30 ... +105 °C unmoved -20 ... +105 °C moved
Impedance	100 Ω
Conductor resistance @ 20 °C	≤216 Ω/km
Insulation resistance @ 20 °C	≥20 MΩ x km

## Material properties

Material (cable)	PVC
Colour (cable)	Colour coded
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

## Commercial data

Packaging size	1
Net weight	2,596 g
Net weight	74 g/m
Country of origin	Germany
European customs tariff number	85444993
GTIN	5713140025196
eCl@ss	27061801 Data and communication cable (copper)
ETIM	EC003249
UNSPSC 24.0	26121609