



**Part Number :** [936010481](#)  
**Product Description :** GWconnect Turned Crimp Contact for 5A D-Sub Inserts and Modules, Male, Gold (Au) Plated Copper Alloy, 0.35-0.50mm<sup>2</sup> (22-20 AWG), 100 per Bag  
**Series Number :** 93601  
**Status :** Active  
**Product Category :** Heavy-Duty Contacts  
**Engineering Number :** 7700.3442.1




Documents & Resources

Drawings  
[936010481\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Part Details

### General

Status	Active
Category	Heavy-Duty Contacts
Series	93601
Description	GWconnect Turned Crimp Contact for 5A D-Sub Inserts and Modules, Male, Gold (Au) Plated Copper Alloy, 0.35-0.50mm <sup>2</sup> (22-20 AWG), 100 per Bag
Contact Type	Turned Crimp
Product Name	GWconnect
UPC	887191892894

### Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

### Physical

Gender	Male
Material - Contact	Copper Alloy
Material - Plating	Gold
Net Weight	0.170/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	5.00mm
Wire Size (AWG)	20, 22
Wire Size mm <sup>2</sup>	0.35-0.50

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
GWconnect Heavy-Duty Connectors and Accessories	<u>93601</u>

Use with Part(s)

Description	Part Number
Use With	D-Sub Connectors

This document was generated on Mar 09, 2025