**Part Number :** 2264611064
**Product Description :** MX64 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, Tin (Sn) Plating, 6 Circuits, Black
**Series Number :** 226461
**Status :** Active
**Product Category :** Power and Signal Cable Assemblies



## Documents and Resources

### Drawings

2264611064_sd.pdf

### 3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Dodecamethylcyclohexasiloxane; Decamethylcyclopentasiloxane; Octamethylcyclotetrasiloxane per D(2025)4165-DC (25 June 2025) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Power and Signal Cable Assemblies |
| Series | 226461 |
| Description | MX64 Female-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, Single Row, 600.00mm Length, Tin (Sn) Plating, 6 Circuits, Black |
| Application | Wire-to-Board, Automotive |
| Assembly Configuration | Single Ended Connector |
| Connector to Connector | MX64-to-Pigtail |
| Product Name | MX64 |
| Type | Discrete Wire Assembly |
| UPC | 198282237075 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 11.0A |
| Voltage - Maximum | 14V DC |

### Physical

| | |
|---|---|
| Cable Length | 600.00mm |
| Circuits (Loaded) | 6 |
| Circuits (maximum) | 6 |
| Color - Resin | Black |
| Gender | Female-Pigtail |

Downloaded from Arrow.com.

| | |
|---|---|
| Lock to Mating Part | Yes |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Tin |
| Material - Plating Termination | Tin |
| Material - Resin | Polybutylene Terephthalate (PBT) |
| Net Weight | 35.674/g |
| Number of Rows | 1 |
| Overmolded | No |
| Packaging Type | Bag |
| Pitch - Mating Interface | 2.54mm |
| Single Ended | Yes |
| Termination Interface Style | Crimp or Compression |
| Wire/Cable Type | TXL |
| Wire Size (AWG) | 20 |



Downloaded from Arrow.com.