



Keyword or Part #

Search

Shop

[Device Networking](#)[IT/Data Center Management](#)[VISIT OUR HOME SITE](#)

Questions? Call Now.

Product Information:

North America: **800-422-7055**
Europe: **+31 (0)76 52 36 744**

Help With Your Order:

North America: **866-649-0721**
Europe: **+31 (0)76 52 36 744**

Technical Support:

North America:
800-422-7044 (US Only)
949-453-7198
Europe: **+31 (0)76 52 36 740**[Home](#) > [IT/Data Center Management](#) >

Lantronix SLP 16 (Phase Out)



Order Info / Part #'s

Product Overview

SLPV1612E-02

Remote Power Mgr; 0U, 16-port, IEC320, 208-230VAC, 50/60Hz

Order Information

Need volume pricing or special requirements?Contact a Lantronix Representative - Call (800) 422-7055 or [Contact Us](#) **U.S.A., Canada, Mexico & International Ordering?**Lantronix products on this online store are only available in the U.S.A., Canada, Mexico & Europe. For worldwide sales, please [Contact a Lantronix Worldwide Sales Office](#) OR [Find a Lantronix partner](#). **Not sure which option is right for you?**

See related products below.

8 Port Models

[SLPH0811E-02](#)

Description

Remote Power Mgr; 1U, 8-port, NEMA, 100-120VAC, 50/60Hz

[SLPH0812E-02](#)

Remote Power Mgr; 1U, 8-port, IEC320, 208-230VAC, 50/60Hz

[SLPH0814G-02*](#)

Remote Power Mgr; 1U, 8-port, IEC320, 208-230VAC, 50/60Hz, L6-30P

[SLPX0811E-02**](#)

Remote Power Expansion Unit; 1U, 8-port, NEMA, 100-120VAC, 50/60Hz

[SLPX0812E-02**](#)

Remote Power Expansion Unit; 1U, 8-port, IEC320, 208-230VAC, 50/60Hz

16 Port Models

[SLPV1611E-02](#)

Description

Remote Power Mgr; 0U, 16-port, NEMA, 100-120VAC, 50/60Hz

[SLPV1612E-02](#)

Remote Power Mgr; 0U, 16-port, IEC320, 208-230VAC, 50/60Hz

[SLPV1614G-02*](#)

Remote Power Mgr; 0U, 16-port, IEC320, 208-230VAC, 50/60Hz, L6-30P

[SLPY1611E-02**](#)

Remote Power Expansion Unit; 0U, 16-port, NEMA, 100-120VAC, 50/60Hz

[SLPY1612E-02**](#)

Remote Power Expansion Unit; 0U, 16-port, IEC320, 208-230VAC, 50/60Hz

*Includes an integrated NEMA-Locking power inlet cord (L6-30P) rated at 230V, 30Amps.

** Includes RJ12 link cable.

The Lantronix SLP Expansion Chassis (SLPX and SLPY) are available in a 8-port and 16-port models. They enable you to attach additional outlets to the master remote power management unit (SLPH and SLPV) via an included RJ12 link cable, and manage separate power circuits from a single IP address and web page.

Optional accessories listed below. One power cord is mandatory for each SLP unit.

Related Accessories

SLPP12410-01 - Power cord:
IEC60320/C19 to NEMA 5-20P
(20A), 10 Ft.

Add

SLPP12310-01 - Power cord:
IEC60320/C19 to NEMA 5-15P
(15A), 8 Ft.

Add

SLPP81107-01 - Power cord:
IEC60320/C13 to
IEC60320/C14, pk. of 8, 6 Ft.

Add

SLPP12510-01 - Power cord:
IEC60320/C19 to NEMA L5-20P
(20A, twist lock), 10 Ft.

Add

SLPM1TH10-01 - Probe:
Temperature and Humidity, 10
Ft. cable

Add

SLPP12610-01 - Power cord:
IEC60320/C19 to NEMA L6-20P
(20A-TWIST), 10 Ft.

Add

500-186-R - Power cord:
IEC60320/C19 to SEV1011
(SWISS), 8 Ft.

Add

Accessories	
SLPP12310-01	Power cord: IEC60320/C19 to NEMA 5-15P (15A), 10 Ft.
SLPP12410-01	Power cord: IEC60320/C19 to NEMA 5-20P (20A), 10 Ft.
SLPP12510-01	Power cord: IEC60320/C19 to NEMA L5-20P (20A, twist lock), 10 Ft.
SLPP12610-01	Power cord: IEC60320/C19 to NEMA L6-20P (20A-TWIST), 10 Ft.
SLPP12810-01	Power cord: IEC60320/C19 to Schuko (EU), 10 Ft.
SLPP12910-01	Power cord: IEC60320/C19 to BS1363 (UK), 10 Ft.
SLPP12A08-01	Power cord: IEC60320/C19 to AS 3112 (AUS/NZ), 10 Ft.
SLPP12B08-01	Power cord: IEC60320/C19 to SI32 (ISRAEL), 8 Ft.
SLPP12C08-01	Power cord: IEC60320/C19 to CHINA/GB (CHINA), 8 Ft.
500-186-R	Power cord: IEC60320/C19 to SEV1011 (SWISS), 8 Ft.
SLPM1TH10-01	Probe: Temperature and Humidity, 10 Ft. cable

SLPP12C08-01 - Power cord: IEC60320/C19 to CHINA/GB (CHINA), 8 Ft.
Add 


SLPP12910-01 - Power cord: IEC60320/C19 to BS1363 (UK), 8 Ft.
Add 


SLPP12B08-01 - Power cord: IEC60320/C19 to SI32 (ISRAEL), 8 Ft.
Add 


SLPP12A08-01 - Power cord: IEC60320/C19 to AS 3112 (AUS/NZ), 8 Ft.
Add 


SLPP12810-01 - Power cord: IEC60320/C19 to Schuko (EU), 8 Ft
Add 


Help Center

[View Cart](#)
[Checkout](#)
[My Account](#)
[Shipping & Returns](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[Contact Us](#)

About Lantronix

Lantronix, Inc. (NASDAQ: LTRX) is a specialized networking company providing M2M (machine to machine) and IoT (Internet of Things) solutions. Our products deliver secure connectivity, device management and mobility for today's increasingly connected world. By networking and managing devices and machines that have never before been connected, we enable our customers to realize the possibilities of the Internet of Things. Founded in 1989, Lantronix pioneers robust, intelligent and easy to deploy solutions for mission critical applications in a wide range of industries, including data center, medical, security, industrial, transportation, retail, financial and government. Lantronix is headquartered in Irvine, California, with offices in Europe, Asia and Japan. For more information, visit www.lantronix.com.

Learn more at the Lantronix blog, www.lantronix.com/blog, featuring industry discussion and updates. To follow Lantronix on Twitter, please visit [www.twitter.com/Lantronix](https://twitter.com/Lantronix). View our video library on YouTube at www.youtube.com/user/LantronixInc or connect with us on LinkedIn at www.linkedin.com/company/lantronix.

Site by [elevator](#)

©2015 Lantronix Inc. All rights reserved.