

## Specification Sheet

Part Number: 151-00018



Clip includes an internal rib that spans the inside of the bracket to fit securely into the profile of the tubing to prevent lateral movement and slipping of the tubing.

Extended fir tree allows for a wide range of panel thicknesses.

Fir tree design provides low insertion forces and high extraction forces.

Convolute Tubing Clip, 0.4" Max Bundle Diameter, Panel Thickness .03"-.24", PA66HIRHS, Black, 500/pkg

|                |           |
|----------------|-----------|
| Article Number | 151-00018 |
|----------------|-----------|

|      |            |
|------|------------|
| Type | CTC10FT6LG |
|------|------------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |     |
|--------------|-----|
| Quantity Per | bag |
|--------------|-----|

|                     |                                                                                                                                                                                                                                                                                                               |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | <p>Convolute Tube Clips provide a quick and easy method for firmly securing corrugated covered cables and wires to a surface.</p> <p>Applications such as this can be found in a wide variety of industries such as the wire harness, automotive, trucking, and heavy equipment manufacturing industries.</p> |
|---------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                   |                                                                                                       |
|-------------------|-------------------------------------------------------------------------------------------------------|
| Short Description | Convolute Tubing Clip, 0.4" Max Bundle Diameter, Panel Thickness .03"-.24", PA66HIRHS, Black, 500/pkg |
|-------------------|-------------------------------------------------------------------------------------------------------|

|                  |                         |
|------------------|-------------------------|
| Global Part Name | CTC10FT6LG-PA66HIRHS-BK |
|------------------|-------------------------|

|                 |          |
|-----------------|----------|
| Fixation Method | Fir Tree |
|-----------------|----------|

|         |       |
|---------|-------|
| Variant | Clips |
|---------|-------|

|                    |      |
|--------------------|------|
| Width W (Imperial) | 0.31 |
|--------------------|------|

|                  |     |
|------------------|-----|
| Width W (Metric) | 8.0 |
|------------------|-----|

|                     |      |
|---------------------|------|
| Height H (Imperial) | 0.85 |
|---------------------|------|

|                   |      |
|-------------------|------|
| Height H (Metric) | 21.4 |
|-------------------|------|

|                             |      |
|-----------------------------|------|
| Nominal Diameter (Imperial) | 0.38 |
|-----------------------------|------|

|                           |      |
|---------------------------|------|
| Nominal Diameter (Metric) | 10.0 |
|---------------------------|------|

|                                |      |
|--------------------------------|------|
| Panel Thickness Min (Imperial) | 0.03 |
|--------------------------------|------|

|                                |      |
|--------------------------------|------|
| Panel Thickness Max (Imperial) | 0.24 |
|--------------------------------|------|

|                              |      |
|------------------------------|------|
| Panel Thickness Min (Metric) | 0.75 |
|------------------------------|------|

|                              |     |
|------------------------------|-----|
| Panel Thickness Max (Metric) | 6.0 |
|------------------------------|-----|

|                                     |             |
|-------------------------------------|-------------|
| Mounting Hole Diameter D (Imperial) | 0.26 - 0.28 |
|-------------------------------------|-------------|

|                                   |              |
|-----------------------------------|--------------|
| Mounting Hole Diameter D (Metric) | 6.5 - 7.0 mm |
|-----------------------------------|--------------|

|                                         |       |
|-----------------------------------------|-------|
| Mounting Hole Diameter D Min (Imperial) | 0.283 |
|-----------------------------------------|-------|

|                                         |                                                                  |
|-----------------------------------------|------------------------------------------------------------------|
| Mounting Hole Diameter D Max (Imperial) | 0.275                                                            |
| Mounting Hole Diameter D Max (Metric)   | 7.0                                                              |
| Disc Diameter (Metric)                  | 16.0                                                             |
| Disc Diameter (Imperial)                | 0.63                                                             |
| Material                                | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) |
| Material Shortcut                       | PA66HIRHS                                                        |
| Flammability                            | UL 94 HB                                                         |
| Operating Temperature                   | -40°F to +221°F (-40°C to +105°C)                                |
| Reach Compliant (Article 33)            | Yes                                                              |
| ROHS Compliant                          | Yes                                                              |
| Package Quantity (Imperial)             | 500                                                              |
| Package Quantity (Metric)               | 500                                                              |
| Customs Number                          | 3926909988                                                       |

