Part Number : 1301380116
Product Description : Super-Safeway Cable Protector, 5-Channel, 0.90m (36.0") Length, Black with Safety Orange Flip Lid
Series Number : 130138
Status : Not Recommended For New Design
Product Category : Connector Accessories
Engineering Part Number : 610-MAIN



Documents and Resources

Drawings

1301380116_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Not Recommended For New Design
Category	Connector Accessories
Series	130138
Description	Super-Safeway Cable Protector, 5-Channel, 0.90m (36.0") Length, Black with Safety Orange Flip Lid
Component Type	Cable Protector
Product Name	Super-Safeway
UPC	78172550940

Physical

Circuits (Loaded)	N/A
Color - Resin	Black, Orange
Height	50.80mm
Length	1.0m
Material - Resin	Polyurethane
Packaging Type	Individual Carton
Temperature Range - Operating	-40° to +48°C
Width	0.50m

Mates With / Use With

Use with Part(s)

Description	Part Number
Super-Safeway Portable Power Distribution Box, Feed-Thru, (6) GFCI Protected NEMA 5-20 Duplex Receptacles, (1) NEMA L6-30 Locking Receptacle, NEMA Type 3R Rainproof	1301380126
Super-Safeway Portable Power Distribution Box, Feed-Thru, (6) GFCI Protected NEMA L5-20 Locking Single Receptacles, (1) NEMA L6-30 Locking Receptacle,	1301380127

Downloaded from Arrow.com.

NEMA Type 3R Rainproof	

This document was generated on Oct 24, 2026

Downloaded from Arrow.com.